



MR16

BC50MRC16/FL36 EXN 3PK

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.


Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	36 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	50 W
Lamp Current (Nom)	4.17 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Energy Consumption kWh/1000 h	53 kWh
Product Data	
Order product name	BC-50MRC16/FL 6/3 TP
Full product name	BC50MRC16/FL36 EXN 3PK
Order code	415802
Material Nr. (12NC)	926000850099
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677415808
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677415803

MR16

Dimensional drawing



Product	D (max)	C (max)
BC-50MRC16/FL 6/3 TP	2-1/16 inch	1-13/16 inch

