

T5 Preheat

F10T5/830 6PK

Philips T5 Fluorescent Lamps are incredibly powerful, environmentally responsible, long life lamps with an ultra-slim profile. This translates into reduced maintenance and disposal costs and also allows the use of smaller fixtures—which reduces ceiling clutter.

Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures (Nom)	8,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	720 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	9.0 W
Lamp Current (Nom)	0.135 A
Voltage (Nom)	67 V
Voltage (Nom)	67 V
Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F10T5/830 6PK
Full product name	F10T5/830 6PK
Order code	927801283003
Material Nr. (12NC)	927801283003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677417277
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677417272

T5 Preheat

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
F10T5/830 6PK	17 mm	403.5 mm	410.6 mm	408.2 mm	417.7 mm

Photometric data



Spectral Power Distribution Colour - F10T5/830 6PK

