



# TUV T8

## TUV 10W T5 with T5-T8 adapters

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

### Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Useful Life (Nom)	9,000 hour(s)
Light Technical	
Color Code	TUV
Color Designation	- [Not Specified]
Depreciation at Useful Lifetime	15 %
Operating and Electrical	
Power Consumption	9 W
Lamp Current (Nom)	0.22 A
Voltage (Nom)	48.5 V

Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
UV	
UV-C Radiation at 100 hr	2.8 W
Product Data	
Order product name	TUV 10W T5 with T5-T8 adapters
Full product name	TUV 10W T5 with T5-T8 adapters
Full product code	871869674408600
Order code	927801304011

Material Nr. (12NC)	927801304011
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696744086
Numerator - Packs per outer box	250


EAN/UPC - Case	8718696744109
----------------	---------------

Dimensional drawing



Product	D (max)	B (max)	B (min)	C (max)	A (max)
TUV 10W T5 with T5-T8 adapters	16 mm	338.6 mm	336.2 mm	345.7 mm	331.5 mm

Photometric data



Spectral Power Distribution Colour – TUV 10W T5 with T5-T8 adapters

