



# TUV T8

## TUV 10W T5 with T5-T8 adapters

TUV T8 lamps are double-ended UV-C 253.7 nm emitting lamps. TUV T8 lamps offer almost constant UV-C output over their complete lifetime. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Useful Life (Nom)	9,000 hour(s)
Light Technical	
Color Code	TUV
Color Designation	- [Not Specified]
Depreciation at Useful Lifetime	15 %
Operating and Electrical	
Power Consumption	9 W
Lamp Current (Nom)	0.22 A
Voltage (Nom)	48.5 V


Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
UV	
UV-C Radiation at 100 hr	2.8 W
Product Data	
Order product name	TUV 10W T5 with T5-T8 adapters
Full product name	TUV 10W T5 with T5-T8 adapters
Full product code	871869674408600
Order code	927801304011
Material Nr. (12NC)	927801304011

TUV T8

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696744086
Numerator - Packs per outer box	250


EAN/UPC - Case	8718696744109
----------------	---------------

Dimensional drawing



Product	D (max)	B (max)	B (min)	C (max)	A (max)
TUV 10W T5 with T5-T8 adapters	16 mm	338.6 mm	336.2 mm	345.7 mm	331.5 mm

Photometric data



Spectral Power Distribution Colour - TUV 10W T5 with T5-T8 adapters

