



Retail Sales T8

F30T8/SW/36 ALTO 6/1

Energy Savings, extra long life, extra low mercury T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	7500 h
Life with 3 Hour Per Day Use	3 a
Features	ALTO® (ALTO)

Light Technical	
Color Code	TL830 [CCT of 3000K (830)]
Initial lumen (Nom)	2500 lm
Color Designation	TL830
Design Mean Lumens	2250 lm
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	85

Operating and Electrical	
Power (Rated) (Nom)	30 W

Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	36
-----------------------	----

Approval and Application	
Picogram Per Lumen Hour	113 pg/lm.h
Mercury (Hg) Content (Nom)	1.9 mg

Product Data	
Order product name	F30T8/SW/36 ALTO 6/1
EAN/UPC - Product	046677392161
Order code	392167
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	927825483003
Net Weight (Piece)	0.001 kg

Warnings and Safety


• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Retail Sales T8

Dimensional drawing

Product

F30T8/SW/36 ALTO 6/1



F30T8/830 36 ALTO

