



MASTER TL-D Super 80

TLDRS16W-S83ECO 25PK

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	8000 h

Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	1220 lm
Luminous Flux (Rated) (Nom)	1220 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	85

Operating and Electrical	
Power (Nom)	16 W
Lamp Current (Nom)	0.265 A

Temperature	
Design Temperature (Nom)	25 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Cap-Base Information	Green Cap

Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	20 kWh


Product Data	
Full product code	872790091767300
Order product name	TLDRS16W-S83ECO 25PK
EAN/UPC - Product	8727900917673
Order code	927850073002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927850073002
Net Weight (Piece)	70.800 g

MASTER TL-D Super 80

Warnings and Safety

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TLDRS16W-S83ECO 25PK	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm



TL-D 16W/830

