



T8 Standard

F17T8/TL841/ALTO 30PK

Philips T8 lamps are energy-efficient lighting solutions.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life 12-hour programme start (hours)	36000 h
Life 12-hour instant start (hours)	30000 h
Life 3-hour programme start (hours)	30000 h
Life 3-hour instant start (hours)	24000 h
Features	ALTO® (ALTO)
Light Technical	
Colour Code	TL841 [CCT of 4,100 K (841)]
Luminous flux (nom.)	1375 lm
Colour designation	TL841
Design mean lumens	1310 lm
Correlated Colour Temperature (Nom)	4100 K
Colour rendering index (nom.)	85
Operating and Electrical	
Power (Rated) (Nom)	17 W

Mechanical and Housing	
Cap-base information	Green Base
Nominal length (inches)	24
Approval and Application	
Energy-saving product	Energy Saving
Picogram per lumen hour	54 pg/lm.h
Mercury (Hg) content (nom.)	1.7 mg


Product Data	
Order product name	F17T8/TL841/ALTO 30PK
EAN/UPC – product	046677281892
Order code	927850084102
SAP numerator – quantity per pack	1
Numerator – packs per outer box	30
SAP material	927850084102
SAP net weight (piece)	0.068 kg

T8 Standard

Dimensional drawing

Product

F17T8/TL841/ALTO 30PK



F17T8/841 24 ALTO ES

