



T8 Standard

F25T8/TL850 ALTO 30PK

Philips T8 lamps are energy-efficient lighting solutions.

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	36000 h
Life 12-Hr Instant Start [Hrs]	30000 h
Life 3-Hr Program Start [Hrs]	30000 h
Life 3-Hr Instant Start [Hrs]	24000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL850 [CCT of 5000K (850)]
Initial lumen (Nom)	2100 lm
Color Designation	TL850
Design Mean Lumens	1995 lm
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	82
Operating and Electrical	
Power (Rated) (Nom)	25 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	36
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	36 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Order product name	F25T8/TL850 ALTO 30PK
EAN/UPC - Product	046677280925
Order code	280925
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927851085002
Net Weight (Piece)	0.102 kg

Warnings and Safety


• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

T8 Standard

Dimensional drawing

Product

F25T8/TL850 ALTO 30PK



F25T8/850 36 ALTO ES

