

T8 Plus

F32T8/TL841 PLUS ALTO HV 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	44000 h
Life 12-Hr Instant Start [Hrs]	36000 h
Life 3-Hr Program Start [Hrs]	38000 h
Life 3-Hr Instant Start [Hrs]	30000 h
Features	ALTO® Plus
Footnotes Fluorescent/CFL 1	Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.

Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Initial lumen (Nom)	2950 lm
Color Designation	TL841
Design Mean Lumens	2800 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	85


Operating and Electrical	
Power (Rated) (Nom)	32 W

Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	48
Bulb Shape	T8 [T8 (T8)]

Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	20 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Order product name	F32T8/TL841 PLUS ALTO HV 30PK
EAN/UPC - Product	046677281793
Order code	281790
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927852084104
Net Weight (Piece)	0.136 kg




T8 Plus

Dimensional drawing

Product

F32T8/TL841 PLUS ALTO HV 30PK



F32T8/841 48 ALTO Plus ES

