



# TuffGuard Coated T8

## F32T8/TL841 PLUS ALTO TG 30PK

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

### Warnings and Safety

- All HO lamps recommended for use only in open fixtures.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information		Operating and Electrical	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	32 W
Features	ALTO® Plus		
Light Technical		Mechanical and Housing	
Color Code	TL841 [CCT of 4100K (841)]	Bulb Shape	T-8 (T8)
Luminous Flux	2,950 lm		
Color Designation	TL841	Approval and Application	
Correlated Color Temperature (Nom)	4100 K	Energy Saving Product	Energy Saving
Color rendering index (CRI)	85	Mercury (Hg) Content (Nom)	1.7 mg
Product Data			
Order product name	F32T8/TL841 PLUS ALTO TG 30PK		
Full product name	F32T8/TL841 PLUS ALTO TG 30PK		

## TuffGuard Coated T8

Order code	283465
Material Nr. (12NC)	927852084105
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677283469

Numerator - Packs per outer box	30
EAN/UPC - Case	50046677283464

### Dimensional drawing

#### Product

F32T8/TL841 PLUS ALTO TG 30PK

