



# U-Bent Rapid Start T8

## FB32T8/TL835/6 ALTO 20PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Product data

| General Information                |   |
|------------------------------------|---|
| Cap-Base                           | G13 [Medium Bi-Pin Fluorescent]           |
| Features                           | ALTO® (ALTO)                              |
| Light Technical                    |   |
| Color Code                         | TL835 [CCT of 3500K (835)]                |
| Luminous Flux                      | 2,800 lm                                  |
| Color Designation                  | TL835                                     |
| Correlated Color Temperature (Nom) | 3500 K                                    |
| Color rendering index (CRI)        | 85  |
| Operating and Electrical           |   |
| Power Consumption                  | 32 W                                      |
| Mechanical and Housing             |   |
| Bulb Shape                         | T8-6U [U-bent T 8/8 inch with 6" spacing] |

| Approval and Application        |                          |
|---------------------------------|--------------------------|
| Energy Saving Product           | Energy Saving            |
| Mercury (Hg) Content (Nom)      | 3.0 mg                   |
| Product Data                    |                          |
| Order product name              | FB32T8/TL835/6 ALTO 20PK |
| Full product name               | FB32T8/TL835/6 ALTO 20PK |
| Order code                      | 379008                   |
| Material Nr. (12NC)             | 927860083502             |
| Numerator - Quantity Per Pack   | 1                        |
| EAN/UPC - Product/Case          | 046677379001             |
| Numerator - Packs per outer box | 20                       |
| EAN/UPC - Case                  | 50046677379006           |

# U-Bent Rapid Start T8

## Dimensional drawing

| Product                  |
|--------------------------|
| FB32T8/TL835/6 ALTO 20PK |

