



U-Bent Rapid Start T8

FB32T8/TL850/6 ALTO 20PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Сар-ваse	G13 [Medium BI-PIN Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL850 [CCT of 5000K (850)]
Luminous Flux	2,750 lm
Color Designation	TL850
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	84
Operating and Electrical	
Power Consumption	32 W
Mechanical and Housing	
Bulb Shape	T8-6U [U-bent T 8/8 inch with 6" spacing]

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
Order product name	FB32T8/TL850/6 ALTO 20PK
Full product name	FB32T8/TL850/6 ALTO 20PK
Order code	927860085003
Material Nr. (12NC)	927860085003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677378806
Numerator - Packs per outer box	20
EAN/UPC - Case	50046677378801

Datasheet, 2023, September 4 data subject to change

U-Bent Rapid Start T8

Dimensional drawing

Product

FB32T8/TL850/6 ALTO 20PK





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.