



# TL-D Standard Colours

## TLDRS16W-CO-25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	8000 h

Light Technical	
Color Code	33-640
Luminous Flux (Nom)	1070 lm
Color Designation	Cool White (CW)
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	83 %
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	63

Operating and Electrical	
Power (Rated) (Nom)	16 W
Lamp Current (Nom)	0.265 A
Voltage (Nom)	70 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	8.0 mg


Product Data	
Full product code	872790091577800
Order product name	TLDRS16W-CO-25
EAN/UPC - Product	8727900915778
Order code	927869003301
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927869003301
Net Weight (Piece)	70.800 g

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## TL-D Standard Colours

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TLDRS16W-CO-25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

TL-D 16W/33-640

