



# MASTER TL-D Super 80

## TLDRS32W-S85ECO 25PK

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	36000 h
Life 12-Hr Instant Start [Hrs]	30000 h
Life 3-Hr Program Start [Hrs]	30000 h
Life 3-Hr Instant Start [Hrs]	24000 h
Footnotes Fluorescent/CFL 1	Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.

Light Technical	
Color Code	TL850 [ CCT of 5000K (850)]
Luminous Flux (Nom)	2650 lm
Color Designation	TL850
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	80

Operating and Electrical	
Power (Rated) (Nom)	32 W

Mechanical and Housing	
Cap-Base Information	Green Cap
Nominal Length (Inch)	48

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg

Product Data	
Full product code	872790091779600
Order product name	TLDRS32W-S85ECO 25PK
EAN/UPC - Product	8727900917796
Order code	927869775002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927869775002
Net Weight (Piece)	134.400 g

## MASTER TL-D Super 80


### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Dimensional drawing

#### Product

TLDRS32W-S85ECO 25PK



F32T8/850

