



TuffGuard Coated T8

F32T8/TL835/ALTO TG 30PK

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Warnings and Safety

- All HO lamps recommended for use only in open fixtures.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Operating and Electrical	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	32 W
Features	ALTO® (ALTO)	Mechanical and Housing	
Light Technical		Bulb Shape	T-8 (T8)
Color Code	TL835 [CCT of 3500K (835)]	Approval and Application	
Luminous Flux	2,850 lm	Energy Saving Product	Energy Saving
Color Designation	TL835	Mercury (Hg) Content (Nom)	1.7 mg
Correlated Color Temperature (Nom)	3500 K	Product Data	
Color rendering index (CRI)	85	Order product name	F32T8/TL835/ALTO TG 30PK
		Full product name	F32T8/TL835/ALTO TG 30PK

TuffGuard Coated T8

Order code	283358
Material Nr. (12NC)	927869783506
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677283353

Numerator - Packs per outer box	30
EAN/UPC - Case	50046677283358

Dimensional drawing

Product
F32T8/TL835/ALTO TG 30PK

