



Rapid Start T8

F40T8/TL835 ALTO 25PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL835 [CCT of 3500K (835)]
Luminous Flux	3,775 lm
Color Designation	TL835
Correlated Color Temperature (Nom)	3500 K
Color rendering index (CRI)	86
Operating and Electrical	
Power Consumption	40 W
Mechanical and Housing	
Bulb Shape	T-8 (T8)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.5 mg
Product Data	
Order product name	F40T8/TL835 ALTO 25PK
Full product name	F40T8/TL835 ALTO 25PK
Order code	368340
Material Nr. (12NC)	927870583501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677368340
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677368345

Rapid Start T8

Dimensional drawing

Product

F40T8/TL835 ALTO 25PK

