



# High Output T8

## F48T8/TL841/HO ALTO 25/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Product data

General Information	
Base	R17D [ R17d (RDC)]
Life 3-Hr Start [Hrs]	18000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL841 [ CCT of 4100K (841)]
Initial lumen (Nom)	4000 lm
Color Designation	TL841
Design Mean Lumens	3600 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	86
Operating and Electrical	
Power (Rated) (Nom)	44 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	48
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	54 pg/lm.h
Mercury (Hg) Content (Nom)	3.5 mg
Product Data	
Order product name	F48T8/TL841/HO ALTO 25/1
EAN/UPC - Product	046677236793
Order code	236794
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927871084104
Net Weight (Piece)	0.001 kg

### Warnings and Safety


• Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

# High Output T8

## Dimensional drawing

### Product

F48T8/TL841/HO ALTO 25/1



F48T8 44W/841 HO ALTO ES

