



TuffGuard Coated T8

F96T8/TL841 PLUS/ALTO TG 25PK

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Warnings and Safety

- All HO lamps recommended for use only in open fixtures.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	FA8 [FA8]
Features	ALTO® Plus
Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Luminous Flux	5,900 lm
Color Designation	TL841
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	85

Operating and Electrical	
Power Consumption	59 W
Mechanical and Housing	
Bulb Shape	T-8 (T8)
Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F96T8/TL841 PLUS/ALTO TG 25PK
Full product name	F96T8/TL841 PLUS/ALTO TG 25PK

TuffGuard Coated T8

Order code	409094
Material Nr. (12NC)	927874584108
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677409098

Numerator - Packs per outer box	25
EAN/UPC - Case	50046677409093

Dimensional drawing

Product
F96T8/TL841 PLUS/ALTO TG 25PK

