

High Output T8

F96T8/D/ALTO

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Base	FA8 [FA8]
Features	ALTO® (ALTO)
Light Technical	
Color Code	765 [CCT of 6500K]
Initial lumen (Nom)	4725 lm
Color Designation	Daylight
Design Mean Lumens	4490 lm
Correlated Color Temperature (Nom)	6500 K
Color Rendering Index (Nom)	76
Operating and Electrical	
Power (Rated) (Nom)	60 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	96
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	98.0 pg/lm.h
Mercury (Hg) Content (Max)	4.4 mg
Product Data	
Order product name	F96T8/D/ALTO
EAN/UPC - Product	046677454128
Order code	454124
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927874776501
Net Weight (Piece)	0.001 kg

Warnings and Safety


• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

High Output T8

Dimensional drawing

Product

F96T8/D/ALTO



F96T8/D/ALTO

