



Preheat T12

F20T12/D/ALTO 15/2

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

| General Information | |
|------------------------------------|----------------------------------|
| Base | G13 [Medium Bi-Pin Fluorescent] |
| Life 3-Hr Start [Hrs] | 9000 h |
| Life with 3 Hour Per Day Use | 4 a |
| Light Technical | |
| Color Code | 54-765 |
| Initial lumen (Nom) | 1075 lm |
| Color Designation | Daylight |
| Design Mean Lumens | 960 lm |
| Correlated Color Temperature (Nom) | 6500 K |
| Color Rendering Index (Nom) | 73 |
| Operating and Electrical | |
| Power (Rated) (Nom) | 20 W |
| Mechanical and Housing | |
| Cap-Base Information | Green Base |

| Nominal Length (Inch) | 24 |
|---------------------------------|-------------------|
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 1.7 mg |
| Product Data | |
| Order product name | F20T12 D ALTO 20W |
| EAN/UPC - Product | 50046677205541 |
| Order code | 205542 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 15 |
| Material Nr. (12NC) | 927883005413 |
| Net Weight (Piece) | 0.500 g |

Warnings and Safety

Preheat T12

Dimensional drawing

Product

F20T12 D ALTO 20W



F20T12/54 24 ALTO

