



Retail Sales T12

F30T12/SOFTWHITE/36 ALTO 6PK

High Performance, Long Life, Environmentally-Responsible Lamps These high performance lamps are ideal for applications where high lumens, long life and high CRI are required.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	18000 h
Life with 3 Hour Per Day Use	7 a
Features	ALTO® (ALTO)
System Description	Rapid Start (RS)

Light Technical	
Color Code	Ultralume 30 [CCT of 3000K (830)]
Initial lumen (Nom)	2400 lm
Color Designation	Ultralume 30
Design Mean Lumens	2160 lm
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	85

Operating and Electrical	
Power (Rated) (Nom)	30 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	36

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	16.0 mg

Product Data	
Order product name	F30T12/SOFTWHITE/36 ALTO 6PK
EAN/UPC - Product	046677392154
Order code	392159
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	927886083006
Net Weight (Piece)	0.001 kg

Warnings and Safety


• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Retail Sales T12

Dimensional drawing

Product

F30T12/SOFTWHITE/36 ALTO 6PK



F30T12/830 RS 36 ALTO

