



TuffGuard Coated T12

F40DX ALTO TG 30PK

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Warnings and Safety

- All HO lamps recommended for use only in open fixtures.

Product data

General Information		Approval and Application	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Energy Saving Product	Not Applicable
Features	ALTO® (ALTO)	Mercury (Hg) Content (Nom)	4.4 mg
Light Technical		Product Data	
Color Code	57	Order product name	F40DX ALTO TG 30PK
Luminous Flux	2,325 lumen	Order code	927888005726
Color Designation	Daylight Deluxe	Numerator - Quantity Per Pack	1
Correlated Color Temperature (Nom)	6500 K	Numerator - Packs per outer box	30
Color rendering index (CRI)	90	Material Nr. (12NC)	927888005726
Operating and Electrical		Full product name	F40DX ALTO TG 30PK
Power Consumption	40 W	EAN/UPC - Case	50046677162998
		EAN/UPC - Product/Case	046677162993
Mechanical and Housing			
Bulb Shape	T-12 (T12)		

TuffGuard Coated T12

Dimensional drawing

Product
F40DX ALTO TG 30PK

