

# High Output T12

## F48T12/D/HO ALTO 15PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

### Product data


| General Information                |                   |
|------------------------------------|-------------------|
| Cap-Base                           | R17D [R17d (RDC)] |
| Features                           | ALTO® (ALTO)      |
| Light Technical                    |                   |
| Color Code                         | 54                |
| Luminous Flux                      | 3,400 lm          |
| Color Designation                  | Daylight          |
| Correlated Color Temperature (Nom) | 6500 K            |
| Color rendering index (CRI)        | 79                |
| Operating and Electrical           |                   |
| Power Consumption                  | 60 W              |
| Mechanical and Housing             |                   |
| Bulb Shape                         | T-12 (T12)        |

| Approval and Application        |                       |
|---------------------------------|-----------------------|
| Energy Saving Product           | Not Applicable        |
| Mercury (Hg) Content (Nom)      | 3.5 mg                |
| Product Data                    |                       |
| Order product name              | F48T12/D/HO ALTO 15PK |
| Full product name               | F48T12/D/HO ALTO 15PK |
| Order code                      | 369843                |
| Material Nr. (12NC)             | 927890205402          |
| Numerator - Quantity Per Pack   | 1                     |
| EAN/UPC - Product/Case          | 046677369842          |
| Numerator - Packs per outer box | 15                    |
| EAN/UPC - Case                  | 50046677369847        |

# High Output T12

## Dimensional drawing

| Product               |
|-----------------------|
| F48T12/D/HO ALTO 15PK |



T12 Recessed Double Contact

