



T5 TuffGuard Coated

F54T5/841/HO/ALTO TG 40PK

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Warnings and Safety

- All HO lamps recommended for use only in open fixtures.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Operating and Electrical	
Cap-Base	G5	Power Consumption	54 W
Features	HO Alto® [High Output Alto]	Lamp Current (Nom)	0.455 A
Light Technical		Controls and Dimming	
Color Code	841 [CCT of 4100K]	Dimmable	Yes
Luminous Flux	5,000 lm	Mechanical and Housing	
Color Designation	Cool White (CW)	Bulb Shape	T5
Correlated Color Temperature (Nom)	4100 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	83 lm/W	Mercury (Hg) Content (Nom)	1.4 mg
Color rendering index (CRI)	82		

T5 TuffGuard Coated

Product Data	
Order product name	F54T5/841/HO/ALTO TG 40PK
Full product name	F54T5/841/HO/ALTO TG 40PK
Order code	162982
Material Nr. (12NC)	927893184102
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	046677162986
Numerator - Packs per outer box	40
EAN/UPC - Case	50046677162981

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F54T5/841/HO/ALTO TG 40PK	11/16 inch	45-1/4 inch	45-9/16 inch	45-7/16 inch	45-13/16 inch

Photometric data




Spectral Power Distribution Colour - F54T5/841/HO/ALTO TG 40PK

Lifetime



Life Expectancy Diagram - F54T5/841/HO/ALTO TG 40PK



Lumen Maintenance Diagram - F54T5/841/HO/ALTO TG 40PK

T5 TuffGuard Coated

Lifetime

Life Expectancy Diagram - F54T5/841/HO/ALTO TG 40PK

