



Rapid Start T12

F96T12/DX/HO/ALTO 15PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap base	R17D [R17d (RDC)]
Life 3-hour start (hours)	12000 h
Features	ALTO® (ALTO)

Light Technical	
Colour Code	57
Luminous flux (nom.)	6750 lm
Design mean lumens	5800 lm
Correlated Colour Temperature (Nom)	6500 K
Colour rendering index (nom.)	90

Operating and Electrical	
Power (Rated) (Nom)	110 W

Mechanical and Housing	
Cap-base information	Green Base

Nominal length (inches)	96
-------------------------	----

Approval and Application	
Mercury (Hg) content (nom.)	6.8 mg

Product Data	
Order product name	F96T12/DX/HO/ALTO 15PK
EAN/UPC – product	046677214890
Order code	927894705701
SAP numerator – quantity per pack	1
Numerator – packs per outer box	15
SAP material	927894705701
SAP net weight (piece)	0.001 kg

Rapid Start T12

Dimensional drawing

Product

F96T12/DX/HO/ALTO 15PK

F96T12 110W/57 HO ALTO®

