



Rapid Start T12

F96T12/DX/HO/ALTO 15PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

| General Information | |
|------------------------------------|-------------------|
| Cap-Base | R17D [R17d (RDC)] |
| Features | ALTO® (ALTO) |
| Light Technical | |
| Color Code | 57 |
| Luminous Flux | 6,750 lm |
| Correlated Color Temperature (Nom) | 6500 K |
| Color rendering index (CRI) | 90 |
| Operating and Electrical | |
| Power Consumption | 110 W |
| Mechanical and Housing | |
| Bulb Shape | T-12 (T12) |

| Approval and Application | |
|---------------------------------|------------------------|
| Mercury (Hg) Content (Nom) | 6.8 mg |
| Product Data | |
| Order product name | F96T12/DX/HO/ALTO 15PK |
| Full product name | F96T12/DX/HO/ALTO 15PK |
| Order code | 214890 |
| Material Nr. (12NC) | 927894705701 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677214890 |
| Numerator - Packs per outer box | 15 |
| EAN/UPC - Case | 50046677214895 |

Rapid Start T12

Dimensional drawing

| Product |
|------------------------|
| F96T12/DX/HO/ALTO 15PK |



T12 Recessed Double Contact

