



High Output T12

TL F96T12/CW/HO-O ALTO 110W FLUOR. LAMP

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap base	R17D [R17d (RDC)]
Life 3-hour start (hours)	12000 h
Features	ALTO® (ALTO)
Footnotes fluorescent/CFL 1	Meets the National Energy Policy Act of 1992 exemption for outdoor or cold temperature applications only. (223)

Light Technical	
Colour Code	33
Luminous flux (nom.)	8800 lm
Colour designation	Cool White (CW)
Design mean lumens	7650 lm
Correlated Colour Temperature (Nom)	4100 K
Colour rendering index (nom.)	62

Operating and Electrical	
Power (Rated) (Nom)	110 W

Mechanical and Housing	
Cap-base information	Green Base
Nominal length (inches)	96

Approval and Application	
Energy-saving product	Not Applicable
Mercury (Hg) content (nom.)	6.8 mg

Product Data	
Order product name	TL F96T12/CW/HO-O ALTO 110W FLUOR. LAMP
EAN/UPC – product	046677381769
Order code	927895203323
SAP numerator – quantity per pack	1
Numerator – packs per outer box	15
SAP material	927895203323
SAP net weight (piece)	0.001 kg

High Output T12

Dimensional drawing

Product

TL F96T12/CW/HO-O ALTO 110W FLUOR. LAMP

F96T12 110W/33 HO ALTO

