

TuffGuard Coated T12

F96T12/CW/HO-O ALTO TG 15PK

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Warnings and Safety

- All HO lamps recommended for use only in open fixtures.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	R17D [R17d (RDC)]
Features	ALTO® (ALTO)
Light Technical	
Color Code	33
Luminous Flux	8,800 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	62

Operating and Electrical	
Power Consumption	110 W
Mechanical and Housing	
Bulb Shape	T-12 (T12)
Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	F96T12/CW/HO-O ALTO TG 15PK
Full product name	F96T12/CW/HO-O ALTO TG 15PK


TuffGuard Coated T12

Order code	163014
Material Nr. (12NC)	927895203332
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677163013

Numerator - Packs per outer box	15
EAN/UPC - Case	50046677163018

Dimensional drawing

Product
F96T12/CW/HO-O ALTO TG 15PK



T12 Reversed Double Contact

