



TL Rapid Start Standard Colours

TLRS110W-ELDNG 15PK

The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	7,500 hour(s)
Light Technical	
Color Code	750 [CCT of 5000K]
Luminous Flux	7,600 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	70
Operating and Electrical	
Power Consumption	110 W
Lamp Current (Nom)	0.790 A
Voltage (Nom)	153 V
Voltage (Nom)	153 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T12 [38 mm (T12)]
Approval and Application	
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	TLRS110W-ELDNG 15PK
Full product name	TLRS110W-ELDNG 15PK
Full product code	872790094378800
Order code	927895275901
Material Nr. (12NC)	927895275901
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900943788
Numerator - Packs per outer box	15
EAN/UPC - Case	8727900943795

TL Rapid Start Standard Colours

Dimensional drawing



Product	D (max)	C (max)
TLRS110W-ELDNG 15PK	40.5 mm	2,385.3 mm

