



# PL-S Short 2-Pin Base

## PL-S 5W/841/2P/ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050


### Product data

General Information	
Cap-Base	G23 [G23]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	250 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	48 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	5.4 W
Lamp Current (Nom)	0.180 A

Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-S 5W/841/2P/ALTO
Full product name	PL-S 5W/841/2P/ALTO
Order code	148684
Material Nr. (12NC)	927900684121
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677148683
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677148688


PL-S Short 2-Pin Base

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-S 5W/841/2P/ALTO	28 mm	13 mm	67 mm	83 mm	105 mm

Photometric data




Spectral Power Distribution Colour - PL-S 5W/841/2P/ALTO

Lifetime



Life Expectancy Diagram - PL-S 5W/841/2P/ALTO



Life Expectancy Diagram - PL-S 5W/841/2P/ALTO

PL-S Short 2-Pin Base

Lifetime



Lumen Maintenance Diagram - PL-S 5W/841/2P/ALTO

