



PL-S 2 Pin

PL-S 7W/840/2P 1CT/25

PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.


Product data

Informasi Umum	
Tutup-Dasar	G23 [G23]
Masa Pakai hingga 50 % Kegagalan (Nom)	8.000 jam
Teknis Lampu	
Kode Warna	840 [CCT of 4000K]
Flux Cahaya	405 lm
Penandaan Warna	Cool White (CW)
Suhu Warna Terkorelasi (Nom)	4100 K
Daya Penerangan (terukur) (Nom)	57 lm/W
Indeks renderasi warna (CRI)	82
Pengoperasian dan Kelistrikan	
Konsumsi Daya	7,1 W
Arus Lampu (Nom)	0,175 A
Tegangan (Nom)	46 V
Tegangan (Nom)	46 V

Kontrol dan Peredupan	
Dapat diredupkan	Tidak
Penyetujuan dan Aplikasi	
Kandungan Merkuri (Hg) (Nom)	1,4 mg
Data Produk	
Nama produk pesanan	PL-S 7W/840/2P 1CT/25
Nama lengkap produk	PL-S 7W/840/2P 1CT/25
Kode produk lengkap	871150070678200
Kode urutan	927901108465
No. Material (12NC)	927901108465
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8711500706782
Numerator - Pak per kotak bagian luar	25
EAN/UPC - Kantung	8711500534019


PL-S 2 Pin

Dimensional drawing



Product	D (max)	D1 (max)	C (max)
PL-S 7W/840/2P 1CT/25	27,1 mm	13 mm	135,5 mm

Photometric data



Spectral Power Distribution Colour - PL-S 7W/840/2P 1CT/25

