



MASTER PL-L 4 Pin 4-針腳型

MASTER PL-L 18W/840/4P 1CT/25

省電型精巧螢光燈管。精巧型長電弧低壓水銀放電燈管。套管內含 2 個平行螢光燈管

安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


产品数据

一般資訊		燈具電流 (標稱)		0.375 A
燈座基底	2G11 [2G11]	控制與調光		
標稱使用壽命	15,000 h	可調光	是	
壽命 (故障率 50%) (標稱)	15,000 h	認證與應用		
照明技術		汞 (Hg) 含量 (標稱)	2.0 mg	
色碼	840 [CCT of 4000K]	能源消耗 kWh/1000 h	20 kWh	
光通量	1,200 lm	產品資料		
色彩名稱	冷白光 (CW)	下訂產品名稱	MASTER PL-L 18W/840/4P 1CT/25	
相關色彩溫度 (規範)	4000 K	完整產品名稱	MASTER PL-L 18W/840/4P 1CT/25	
光效 (額定) (標準)	67 lm/W	完整產品代碼	871150070669041	
演色性指數 (CRI)	82	訂單代碼	927903008472	
運轉與電力		材質 Nr. (12NC)	927903008472	
耗電量	18.0 W	分子 - 每個包裝的數量	1	

MASTER PL-L 4 Pin 4-針腳型


EAN/UPC - 產品/案例	8711500706690
分子 - 每一外盒包裝	25
EAN/UPC - 箱	8711500610652

二维绘图



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 18W/840/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm

光度数据



Spectral Power Distribution Colour - MASTER PL-L 18W/840/4P 1CT/25

