



# MASTER PL-L 4 Pin

## MASTER PL-L 18W/840/4P 1CT/25

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Color rendering index (CRI)	
Cap-Base	2G11 [2G11]	82	
Nominal lifetime	15,000 hour(s)	Operating and Electrical	
Life to 50% Failures (Nom)	15,000 hour(s)	Power Consumption	18.0 W
		Lamp Current (Nom)	0.375 A
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	1,200 lm	Approval and Application	
Color Designation	Cool White (CW)	Mercury (Hg) Content (Nom)	2.0 mg
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	67 lm/W		

MASTER PL-L 4 Pin

Energy Consumption kWh/1000 h	20 kWh
Product Data	
Order product name	MASTER PL-L 18W/840/4P 1CT/25
Full product name	MASTER PL-L 18W/840/4P 1CT/25
Full product code	871150070669041
Order code	927903008472


Material Nr. (12NC)	927903008472
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500706690
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500610652

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 18W/840/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 18W/840/4P 1CT/25

