



MASTER PL-L 4 Pin

MASTER PL-L 36W/840/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Correlated Color Temperature (Nom)	
Cap-Base	2G11 [2G11]	4000 K	
Flux measurement reference	Sphere	Luminous Efficacy (rated) (Nom)	
Life to 50% Failures (Nom)	15,000 hour(s)	81 lm/W	
		Color rendering index (CRI)	
		80	
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Power Consumption	
Luminous Flux	2,850 lm	36.3 W	
Color Designation	Cool White (CW)	Lamp Current (Nom)	
Chromaticity Coordinate X (Nom)	0.38	0.435 A	
Chromaticity Coordinate Y (Nom)	0.38	Controls and Dimming	
		Dimmable	
		Yes	

MASTER PL-L 4 Pin

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2 mg
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	37 kWh
EPREL Registration Number	423271
Product Data	
Order product name	MASTER PL-L 36W/840/4P 1CT/25
Full product name	MASTER PL-L 36W/840/4P 1CT/25


Full product code	871150070675140
Order code	927903408470
Material Nr. (12NC)	927903408470
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500706751
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500711014

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 36W/840/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 36W/840/4P 1CT/25

