



MASTER PL-L 4 Pin



MASTER PL-L 36W/840/4P 1CT/25

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- · Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	2G11
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	2,850 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K

Luminous Efficacy (rated) (Nom)	81 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	36.3 W
Lamp Current (Nom)	0.435 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G


Datasheet, 2024, February 8 data subject to change

MASTER PL-L 4 Pin

Mercury (Hg) Content (Max)	2 mg
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	37 kWh
EPREL Registration Number	423271
Product Data	
Order product name	MASTER PL-L 36W/840/4P 1CT/25
Full product name	MASTER PL-L 36W/840/4P 1CT/25
Full product code	871150070675140

Order code	927903408470
Material Nr. (12NC)	927903408470
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500706751
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500711014


Dimensional drawing



 Product
 D (max)
 D1 (max)
 A (max)
 B (max)
 C (max)

 MASTER PL-L 36W/840/4P 1CT/25
 39.0 mm
 18.0 mm
 384.2 mm
 410 mm
 416.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 36W/840/4P 1CT/25



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.