



MASTER PL-L 4 Pin 4-針腳型

MASTER PL-L 36W/840/4P 1CT/25

省電型精巧螢光燈管。精巧型長電弧低壓水銀放電燈管。套管內含 2 個平行螢光燈管

安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	2G11
標稱使用壽命	15,000 h
壽命 (故障率 50%) (標稱)	15,000 h

照明技術	
色碼	840 [CCT of 4000K]
光通量	2,900 lm
色彩名稱	冷白光 (CW)
相關色彩溫度 (規範)	4100 K
光效 (額定) (標準)	81 lm/W
演色性指數 (CRI)	82

運轉與電力	
耗電量	36.0 W

燈具電流 (標稱)	0.435 A
-----------	---------

控制與調光	
可調光	是


認證與應用	
汞 (Hg) 含量 (標稱)	2.0 mg
能源消耗 kWh/1000 h	40 kWh

產品資料	
下訂產品名稱	MASTER PL-L 36W/840/4P 1CT/25
完整產品名稱	MASTER PL-L 36W/840/4P 1CT/25
完整產品代碼	871150070675141
訂單代碼	927903408472
材質 Nr. (12NC)	927903408472
分子 - 每個包裝的數量	1

MASTER PL-L 4 Pin 4-針腳型


EAN/UPC - 產品/案例	8711500706751
分子 - 每一外盒包裝	25
EAN/UPC - 箱	8711500711014

二维绘图



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 36W/840/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

光度数据



Spectral Power Distribution Colour - MASTER PL-L 36W/840/4P 1CT/25

