



MASTER PL-C 2 Pin

MASTER PL-C 13W/830/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 4 parallel narrow fluorescent tubes

Product data

General Information	
Cap base	G24D-1 [G24d-1]
Life to 10% failures (nom.)	6500 h
Life to 50% failures (nom.)	10000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	92 %
LSF 8000 h Rated	78 %
Light Technical	
Colour code	830 [CCT of 3,000 K]
Luminous flux (nom.)	925 lm
Luminous flux (rated) (nom.)	925 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	69 lm/W
Color rendering index (nom.)	82
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	13.4 W

Lamp current (nom.)	0.170 A
Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	no
Mechanical and Housing	
Cap base information	2P
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	17 kWh
Product Data	
Full product code	871150062084270
Order product name	MASTER PL-C 13W/830/2P 1CT/5X10BOX
EAN/UPC – product	8711500620842
Order code	62084270
Local Code	13PLC8302PIN
Numerator – quantity per pack	1
Numerator – packs per outer box	50
Material no. (12NC)	927904883040


MASTER PL-C 2 Pin

Net weight (piece)	53.600 g
ILCOS Code	FSQ-13/30/1B-I-G24d=1

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm

PL-C 13W/830/2P

Photometric data



Lightcolour /830



Lightcolour /830

MASTER PL-C 2 Pin

Lifetime

