



MASTER PL-C 2 Pin

MASTER PL-C 13W/840/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Warnings and Safety

- Use only with electromagnetic control gear
- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	G24D-1 [G24d-1]	Chromaticity Coordinate Y (Nom)	0.38
Flux measurement reference	Sphere	Correlated Color Temperature (Nom)	4000 K
Life to 50% Failures (Nom)	10,000 hour(s)	Luminous Efficacy (rated) (Nom)	69 lm/W
		Color rendering index (CRI)	80
Light Technical			
Color Code	840 [CCT of 4000K]	Power Consumption	13.8 W
Luminous Flux	925 lm	Lamp Current (Nom)	0.170 A
Color Designation	Cool White (CW)		
Chromaticity Coordinate X (Nom)	0.38		

MASTER PL-C 2 Pin

Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	14 kWh
EPREL Registration Number	423280
Product Data	
Order product name	MASTER PL-C 13W/840/2P 1CT/5X10BOX


Full product name	MASTER PL-C 13W/840/2P 1CT/5X10BOX
Full product code	871150062086670
Order code	927904884040
Material Nr. (12NC)	927904884040
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500620866
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500715692

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/840/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm



Photometric data




Spectral Power Distribution Colour - MASTER PL-C 13W/840/2P 1CT/5X10BOX

MASTER PL-C 2 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-C 13W/840/2P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 13W/840/2P 1CT/5X10BOX

Lumen Maintenance Diagram - MASTER PL-C 13W/840/2P 1CT/5X10BOX

