



PL-C Cluster 2-Pin Base

PL-C ALTO 13W/830 GX23-2 /2P 1CT

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information	
Cap-Base	GX23-2 [GX23-2]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	780 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	61 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	12.7 W

Lamp Current (Nom)	0.285 A
Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-C ALTO 13W/830 GX23-2 /2P 1CT
Full product name	PL-C ALTO 13W/830 GX23-2 /2P 1CT
Order code	383117
Material Nr. (12NC)	927904983030
Numerator - Quantity Per Pack	1

PL-C Cluster 2-Pin Base


EAN/UPC - Product/Case	046677114923
Numerator - Packs per outer box	10
EAN/UPC - Case	60046677114925

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C ALTO 13W/830	1-1/16 inch	1-1/16 inch	3-3/16 inch	3-15/16 inch	4-13/16 inch
GX23-2 /2P 1CT					

Photometric data




Spectral Power Distribution Colour - PL-C ALTO 13W/830 GX23-2 /2P 1CT

Lifetime



Life Expectancy Diagram - PL-C ALTO 13W/830 GX23-2 /2P 1CT



Life Expectancy Diagram - PL-C ALTO 13W/830 GX23-2 /2P 1CT

PL-C Cluster 2-Pin Base

Lifetime



Lumen Maintenance Diagram - PL-C ALTO 13W/830 GX23-2 /2P 1CT

