



MASTER PL-C 2 Pin



MASTER PL-C 26W/827/2P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G24D-3 [G24d-3]
Life to 10% failures (nom.)	6500 h
Life to 50% failures (nom.)	10000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	92 %
LSF 8000 h Rated	78 %
	Sphere

Luminous flux (nom.)	1800 lm
Luminous flux (rated) (nom.)	1800 lm
Colour designation	Incandescent White
Chromaticity coordinate X (nom.)	0.463
Chromaticity coordinate Y (nom.)	0.42
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	68 lm/W
Colour rendering index (nom.)	81
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	83 %


Light Technical	
Colour Code	827 [CCT of 2,700 K]

MASTER PL-C 2 Pin

LLMF 8000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	26.5 W
Lamp current (nom.)	0.335 A
Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Cap-base information	2P
Approval and Application	
Energy Efficiency Class	G

Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	27 kWh
	423286
Product Data	
Full product code	871150062095870
Order product name	MASTER PL-C 26W/827/2P 1CT/5X10BOX
EAN/UPC – product	8711500620958
Order code	62095870
SAP numerator – quantity per pack	1
Numerator – packs per outer box	50
SAP material	927906182740
SAP net weight (piece)	64.300 g
ILCOS code	FSQ-26/27/1B-I-G24d=3


Dimensional drawing




PL-C 26W/827/2P

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 26W/827/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

Photometric data



LDPB_PLC2P_827-Spectral power distribution B/W



Lightcolour /827

MASTER PL-C 2 Pin

Lifetime



LDLE_PLC2P_0001-Life expectancy diagram

LDLE_PLC2P_0002-Life expectancy diagram



LDLM_PLC2P_0001-Lumen maintenance diagram

