



MASTER PL-C 2 Pin

MASTER PL-C 26W/865/2P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General information		Operating and electrical	
Cap-Base	G24D-3 [G24d-3]	Luminous Flux (Rated) (Nom)	1740 lm
Life To 10% Failures (Nom)	6500 h	Color Designation	Cool Daylight
Life to 50% Failures (Nom)	10000 h	Correlated Color Temperature (Nom)	6500 K
LSF 2000 h Rated	99 %	Luminous Efficacy (rated) (Nom)	66 lm/W
LSF 4000 h Rated	98 %	Color Rendering Index (Nom)	80
LSF 6000 h Rated	92 %	LLMF 2000 h Rated	90 %
LSF 8000 h Rated	78 %	LLMF 4000 h Rated	85 %
		LLMF 6000 h Rated	81 %
		LLMF 8000 h Rated	77 %
Light technical			
Color Code	865 [CCT of 6500K]	Power (Nom)	26.5 W
Luminous Flux (Nom)	1740 lm		

MASTER PL-C 2 Pin

Lamp Current (Nom)	0.335 A
Temperature	
Design Temperature (Nom)	28 °C
Controls and dimming	
Dimmable	No
Mechanical and housing	
Cap-Base Information	2 Pins
Approval and application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	32 kWh

Product data	
Full product code	871150063531000
Order product name	MASTER PL-C 26W/865/2P 1CT/5X10BOX
EAN/UPC - Product	8711500635310
Order code	927906186502
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	927906186502
Net Weight (Piece)	64.300 g
ILCOS Code	F5Q-26/65/1B-I-G24d=3


Dimensional drawing




MASTER PL-C 26W/865/2P 1CT/5X10BOX

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 26W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

Photometric data



LDPB_PLC2P_865-Spectral power distribution B/W



LDPO_PLC2P_865-Spectral power distribution Colour

MASTER PL-C 2 Pin

Lifetime



LDLE_PLC2P_0001-Life expectancy diagram

LDLE_PLC2P_0002-Life expectancy diagram



LDLM_PLC2P_0001-Lumen maintenance diagram

