



MASTER PL-C 2 Pin

MASTER PL-C 26W/865/2P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

Product data

General Information	
Cap-Base	G24D-3 [G24d-3]
Life To 10% Failures (Nom)	6500 h
Life to 50% Failures (Nom)	10000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	92 %
LSF 8000 h Rated	78 %
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux (Nom)	1740 lm
Luminous Flux (Rated) (Nom)	1740 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	66 lm/W
Color Rendering Index (Nom)	80
LLMF 2000 h Rated	90 %
LLMF 4000 h Rated	85 %
LLMF 6000 h Rated	81 %

LLMF 8000 h Rated	77 %
Operating and Electrical	
Power (Rated) (Nom)	26.5 W
Lamp Current (Nom)	0.335 A
Temperature	
Design Temperature (Nom)	28 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Cap-Base Information	2P
Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	32 kWh

MASTER PL-C 2 Pin


Product Data	
Full product code	871150063531070
Order product name	MASTER PL-C 26W/865/2P 1CT/5X10BOX
EAN/UPC - Product	8711500635310
Order code	927906186540
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	50
Material Nr. (12NC)	927906186540
Net Weight (Piece)	64.300 g
ILCOS Code	FSQ-26/65/1B-I-G24d=3

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




PL-C 26W/865/2P

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 26W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

Photometric data




Lightcolor /865




Lightcolor /865

MASTER PL-C 2 Pin

Lifetime



Life Expectancy 3 h cycle



Life Expectancy 12 h cycle

Lumen Maintenance 3h + 12 h cycle

