



MASTER PL-C 2 Pin 2-針腳型

MASTER PL-C 26W/865/2P 1CT/5X10BOX

省電型精巧螢光燈管精巧型長電弧低壓水銀放電燈管套管內含 4 個平行細長螢光燈管

產品數據

基本資訊	
接口	G24D-3 [G24d-3]
至 10% 故障的使用時間 (標稱)	6500 h
至 50% 故障的使用時間 (標稱)	10000 h
額定 LSF (預熱 2000 小時), 3 小時	99 %
額定 LSF (預熱 4000 小時), 3 小時	98 %
額定 LSF (預熱 6000 小時), 3 小時	92 %
額定 LSF (預熱 8000 小時), 3 小時	78 %

照明科技	
色碼	865 [CCT of 6500K]
光通量 (標稱)	1740 lm
光通量 (額定) (標稱)	1740 lm
色彩名稱	冷日光
相關色溫 (標稱)	6500 K
光效 (額定) (標稱)	66 lm/W
演色性指數 (標稱)	80
額定 SLMF (2000 小時)	90 %
額定 SLMF (4000 小時)	85 %
額定 SLMF (6000 小時)	81 %
額定 SLMF (8000 小時)	77 %

運作和電氣	
Power (Rated) (Nom)	26.5 W
燈具電流 (標稱)	0.335 A

溫度	
設計溫度 (標稱)	28 °C

控制調光	
可調光	No

機械和殼體	
接口資訊	2P

應用	
能源效益標籤 (EEL)	B
汞 (Hg) 含量 (標稱)	1.4 mg
能源消耗 kWh/1000 h	32 kWh

產品參數	
完整產品碼	871869960680000
訂購產品名稱	MASTER PL-C 26W/865/2P 1CT/5X10BOX
EAN/UPC - 產品	8718699606800
訂購代碼	927906186565

MASTER PL-C 2 Pin 2-針腳型


分子 - 各件數量	1
分子 - 每一外盒內件數	50
材質編號(12NC)	927906186565
淨重 (件)	64.300 g

ILCOS Code	FSQ-26/65/1B-I-G24d=3
------------	-----------------------

安全提示

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



二维绘图



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 26W/865/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

PL-C 26W/865/2P

光度数据



MASTER PL-C 2 Pin 2-針腳型

壽命

