



# MASTER PL-C Xtra 2 Pin

## MASTER PL-C XTRA 26W/830/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 4 parallel narrow fluorescent tubes

### Product data

General Information		LLMF 8000 h Rated		81 %	
Cap base	G24D-3 [ G24d-3]	LLMF 12000 h Rated	79 %		
Life to 10% failures (nom.)	12000 h	LLMF 16000 h Rated	78 %		
Life to 50% failures (nom.)	16000 h	LLMF 20000 h Rated	77 %		
LSF 2000 h Rated	99 %	<b>Operating and Electrical</b>			
LSF 4000 h Rated	98 %	Power (Rated) (Nom)	26 W		
LSF 6000 h Rated	97 %	Lamp current (nom.)	0.325 A		
LSF 8000 h Rated	95 %	<b>Temperature</b>			
LSF 12000 h Rated	90 %	Design temperature (nom.)	28 °C		
LSF 16000 h Rated	50 %	<b>Controls and Dimming</b>			
<b>Light Technical</b>		Dimmable	no		
Colour code	830 [ CCT of 3,000 K]	<b>Mechanical and Housing</b>			
Luminous flux (nom.)	1800 lm	Cap base information	2P		
Luminous flux (rated) (nom.)	1800 lm	<b>Approval and Application</b>			
Colour designation	Warm white (WW)	Energy efficiency label (EEL)	B		
Correlated colour temperature (nom.)	3000 K	Mercury (Hg) content (nom.)	3.0 mg		
Luminous efficacy (rated) (nom.)	68 lm/W				
Color rendering index (nom.)	>80				
LLMF 2000 h Rated	92 %				
LLMF 4000 h Rated	87 %				
LLMF 6000 h Rated	83 %				

# MASTER PL-C Xtra 2 Pin


Energy Consumption kWh/1000 h	32 kWh
<b>Product Data</b>	
Full product code	871150089883870
Order product name	MASTER PL-C Xtra 26W/830/2P 1CT/5X10BOX
EAN/UPC – product	8711500898838
Order code	89883870
Local Code	26PLC8302PXTRA

Numerator – quantity per pack	1
Numerator – packs per outer box	50
Material no. (12NC)	927906283014
Net weight (piece)	64.300 g
ILCOS Code	FSQ-26/30/1B-I-G24d=3

## Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C Xtra 26W/ 830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.7 mm	149.0 mm	171.4 mm

PL-C Xtra 26W/830/2P

## Photometric data



Lightcolour /830



Lightcolour /830

# MASTER PL-C Xtra 2 Pin

## Lifetime

