



MASTER PL-C Xtra 2 Pin

MASTER PL-C XTRA 26W/830/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp current (nom.)	
Cap base	G24D-3 [G24d-3]	0.325 A	
Life to 50% failures (nom.)	16,000 h	Controls and Dimming	
Light Technical		Dimmable	No
Colour Code	830 [CCT of 3000K]	Approval and Application	
Luminous Flux	1,800 lm	Mercury (Hg) content (nom.)	3.0 mg
Colour designation	Warm White (WW)	Energy consumption kWh/1,000 hours 32 kWh	
Correlated Colour Temperature	3000 K	Product Data	
Luminous efficacy (rated) (nom.)	68 lm/W	Order product name	MASTER PL-C Xtra 26W/830/2P 1CT/5X10BOX
Colour rendering index (CRI)	>80	Full product name	MASTER PL-C XTRA 26W/830/2P 1CT/5X10BOX
Operating and Electrical		Full EOC	871150089883870
Power Consumption	26 W	Order code	89883870

MASTER PL-C Xtra 2 Pin

Material no. (12 NC)	927906283014
Local order code	26PLC8302PXTRA
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500898838

Numerator – packs per outer box	50
EAN/UPC – Case	8711500898852

Dimensional drawing





Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C Xtra 26W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.7 mm	149.0 mm	171.4 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-C Xtra 26W/830/2P 1CT/5X10BOX

Lifetime




Life Expectancy Diagram - MASTER PL-C Xtra 26W/830/2P 1CT/5X10BOX


Life Expectancy Diagram - MASTER PL-C Xtra 26W/830/2P 1CT/5X10BOX

MASTER PL-C Xtra 2 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-C Xtra 26W/830/2P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-C Xtra 26W/830/2P 1CT/5X10BOX

