



# MASTER PL-C 4 Pin

## MASTER PL-C 10W/840/4P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G24Q-1 [G24q-1]
Flux measurement reference	Sphere
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	600 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K


Luminous Efficacy (rated) (Nom)	60 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	10.4 W
Lamp Current (Nom)	0.190 A
Controls and Dimming	
Dimmable	Yes

MASTER PL-C 4 Pin

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	11 kWh
EPREL Registration Number	423297
Product Data	
Order product name	MASTER PL-C 10W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-C 10W/840/4P 1CT/5X10BOX


Full product code	871150062330070
Order code	927907084040
Material Nr. (12NC)	927907084040
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500623300
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500711038

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 10W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	75.5 mm	95.0 mm	109.9 mm



Photometric data




Spectral Power Distribution Colour - MASTER PL-C 10W/840/4P 1CT/5X10BOX

MASTER PL-C 4 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-C 10W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 10W/840/4P 1CT/5X10BOX

Lumen Maintenance Diagram - MASTER PL-C 10W/840/4P 1CT/5X10BOX

