



MASTER PL-C 4 Pin

MASTER PL-C 13W/830/4P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical	
Cap-Base	G24Q-1 [G24q-1]	Correlated Color Temperature (Nom)	3000 K
Life to 50% Failures Preheat (Nom)	13000 h	Luminous Efficacy (rated) (Nom)	72 lm/W
LSF Preheat 2000 h Rated	99 %	Color Rendering Index (Nom)	82
LSF Preheat 4000 h Rated	98 %	LLMF 2000 h Rated	92 %
LSF Preheat 6000 h Rated	97 %	LLMF 4000 h Rated	87 %
LSF Preheat 8000 h Rated	90 %	LLMF 6000 h Rated	83 %
		LLMF 8000 h Rated	81 %
Light Technical		Operating and Electrical	
Color Code	830 [CCT of 3000K]	Power (Nom)	13.0 W
Luminous Flux (Nom)	900 lm	Lamp Current (Nom)	0.170 A
Luminous Flux (Rated) (Nom)	900 lm		
Color Designation	Warm White (WW)		

MASTER PL-C 4 Pin

Temperature

Design Temperature (Nom)	28 °C
--------------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-Base Information	4 Pins
----------------------	--------


Approval and Application

Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	15 kWh

Product Data

Full product code	871150062331700
Order product name	MASTER PL-C 13W/830/4P 1CT/5X10BOX
EAN/UPC - Product	8711500623317
Order code	927907183001
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	927907183001
Net Weight (Piece)	49.900 g
ILCOS Code	FSQ-13/30/1B-E-G24q=1


Dimensional drawing




PL-C 13W/830/4P

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/830/4P 1CT/5X10CC	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm

Photometric data




LDPB_PLC4P_830-Spectral power distribution B/W



LDPO_PLC4P_830-Spectral power distribution Colour


MASTER PL-C 4 Pin

Lifetime



LDLE_PLC4P_0001-Life expectancy diagram

LDLE_PLC4P_0002-Life expectancy diagram



LDLM_PLC4P_0001-Lumen maintenance diagram

