



# PL-C Cluster 4-Pin Base

## PL-C 13W/835/4P/ALTO 10PK

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Product data

General Information	
Cap-Base	G24Q-1 [ G24q-1]
Life to 50% Failures Preheat (Nom)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light Technical	
Color Code	835 [ CCT of 3500K]
Luminous Flux (Nom)	925 lm
Luminous Flux (Rated) (Nom)	925 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	69 lm/W
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	83 %


LLMF 8000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	13.0 W
Lamp Current (Nom)	0.170 A
Temperature	
Design Temperature (Nom)	28 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	4P
Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg

# PL-C Cluster 4-Pin Base

Energy Consumption kWh/1000 h	15 kWh
<b>Product Data</b>	
Order product name	PL-C 13W/835/4P/ALTO 10PK
EAN/UPC - Product	046677237745
Order code	383273

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927907183530
Net Weight (Piece)	49.900 g



## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C 13W/835/4P/ALTO 10PK	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm

PL-C ALTO 13W/835/4P



## Photometric data



Lightcolor /835

Lightcolor /835

## Lifetime




Life Expectancy 3 h cycle

Life Expectancy 12 h cycle

## PL-C Cluster 4-Pin Base

### Lifetime



Lumen Maintenance 3 h and 12 h cycle

