



MASTER PL-C 4 Pin

MASTER PL-C 13W/840/4P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	G24Q-1 [G24q-1]	0.170 A	
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	925 lm	Approval and Application	
Color Designation	Cool White (CW)	Mercury (Hg) Content (Nom)	1.4 mg
Correlated Color Temperature (Nom)	4000 K	Energy Consumption kWh/1000 h	15 kWh
Luminous Efficacy (rated) (Nom)	69 lm/W	Product Data	
Color rendering index (CRI)	82	Order product name	MASTER PL-C 13W/840/4P 1CT/5X10BOX
Operating and Electrical		Full product name	MASTER PL-C 13W/840/4P 1CT/5X10BOX
Power Consumption	13.0 W	Full product code	871150062332400

MASTER PL-C 4 Pin

Order code	927907184002
Material Nr. (12NC)	927907184002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500623324


Numerator - Packs per outer box	50
EAN/UPC - Case	8711500715739

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-C 13W/840/4P 1CT/5X10BOX

Lifetime



Life Expectancy Diagram - MASTER PL-C 13W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 13W/840/4P 1CT/5X10BOX

MASTER PL-C 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-C 13W/840/4P 1CT/5X10BOX

