



MASTER PL-C 4 Pin

MASTER PL-C 13W/865/4P 1CT/5X10BOX

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 4 parallel narrow fluorescent tubes


Product data

General Information	
Cap base	G24Q-1 [G24q-1]
Life to 50% failures preheat (nom.)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light Technical	
Colour Code	865 [CCT of 6,500 K]
Lamp Luminous Flux 25°C EL (Nom)	845 lm
Lamp Luminous Flux (Nom)	845 lm
Colour Designation	Cool Daylight
Colour Temperature, horizontal (Nom)	6500 K
Lamp Luminous Efficacy EM (Nom)	63 lm/W
Colour Rendering Index, horiz (Nom)	80
LLMF 2000 h Rated	90 %
LLMF 4000 h Rated	85 %
LLMF 6000 h Rated	81 %
LLMF 8000 h Rated	77 %
Operating and Electrical	
Power (Rated) (Nom)	13.0 W
Lamp current (nom.)	0.170 A

Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Cap base information	4P
Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	15 kWh
Product Data	
Full product code	871150027703900
Order product name	MASTER PL-C 13W/865/4P 1CT/5X10BOX
EAN/UPC – product	8711500277039
Order code	927907186501
Numerator – quantity per pack	1
Numerator – packs per outer box	50
Material no. (12NC)	927907186501
Net weight (piece)	49.900 g

MASTER PL-C 4 Pin


Dimensional drawing




PL-C 13W/865/4P

Product
MASTER PL-C 13W/865/4P 1CT/5X10BOX

Photometric data




LDPE_PLC4P_865-Spectral power distribution B/W




LDPO_PLC4P_865-Spectral power distribution Colour

Lifetime



LDLE_PLC4P_0001-Life expectancy diagram



LDLE_PLC4P_0002-Life expectancy diagram

MASTER PL-C 4 Pin

Lifetime



LDLM_PLC4P_0001-Lumen maintenance diagram

